

Pneumatic module for 3 contacts



Part number	09 14 003 3501
Specification	Pneumatic module for 3 contacts
HARTING eCatalogue	https://b2b.harting.com/09140033501

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Pneumatic module

Version

Gender	Male Female
Number of contacts	3
Details	Please order contacts separately.

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polycarbonate
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61984 EN 60664-1
----------------	-------------------------



Pushing Performance

Commercial data

Packaging size	1
Net weight	7.68 g
Country of origin	Germany
Customs tariff number	39269097
