

UNI-DICHT-HALB-Verschraubung Pg16



Part number	09 00 000 5058
Specification	UNI-DICHT-HALB-Verschraubung Pg16
HARTING eCatalogue	https://b2b.harting.com/09000005058

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for surface mounted housings

Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	6 Nm
Wrench size	A/F 27
Degree of protection acc. to IEC 60529	IP65
Size	Pg 16
Clamping range	11.5 ... 15.5 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (accessories)	Black
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	10
Net weight	5.83 g



Pushing Performance

Commercial data

Country of origin	Germany
Customs tariff number	84849000
