

Uni-Dicht-Verschraubung Pg13,5 6,5-9,5mm



Part number	09 00 000 5083
Specification	Uni-Dicht-Verschraubung Pg13,5 6,5-9,5mm
HARTING eCatalogue	https://b2b.harting.com/09000005083

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +130 °C
Tightening torque	10 Nm
Wrench size	A/F 22
Degree of protection acc. to IEC 60529	IP68
Size	Pg 13.5
Clamping range	6.5 ... 9.5 mm

Material properties

Material (cable glands)	Metal
Colour (accessories)	Black
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	10
Net weight	32.4 g
Country of origin	Germany



Pushing Performance

Commercial data

Customs tariff number	84849000
-----------------------	----------
