

## Uni-Dicht-Verschraubung Pg 16, 6,5-9,5mm



Part number	09 00 000 5086
Specification	Uni-Dicht-Verschraubung Pg 16, 6,5-9,5mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09000005086">https://b2b.harting.com/09000005086</a>

### Identification

Category	Accessories
Type of accessory	Cable gland

### Technical characteristics

Limiting temperature	-40 ... +130 °C
Tightening torque	10 Nm
Wrench size	A/F 24
Degree of protection acc. to IEC 60529	IP68
Size	Pg 16
Clamping range	6.5 ... 9.5 mm

### Material properties

Material (cable glands)	Metal
Colour (accessories)	Black
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Commercial data

Packaging size	10
Net weight	38.9 g
Country of origin	Germany



Pushing Performance

## Commercial data

Customs tariff number	84849000
-----------------------	----------

---