

## Han CGM-M M20x1,5 D.5-9mm/6-12mm



Part number	19 00 000 5081
Specification	Han CGM-M M20x1,5 D.5-9mm/6-12mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005081">https://b2b.harting.com/19000005081</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M
Type of accessory	Cable gland

### Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	10 Nm
Wrench size	A/F 22
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	5 ... 12 mm
Width across corners	24.4 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Brass, nickel plated
Material (clamping ring)	Polyamide
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Specifications and approvals

Approvals	DNV GL
-----------	--------



Pushing Performance

## Specifications and approvals

UL / CSA	UL 514B QCRV.E479780
	CSA-C22.2 No. 18.3 QCRV7.E479780

## Commercial data

Packaging size	10
Net weight	29.8 g
Country of origin	Germany
Customs tariff number	84849000