

Han CGM-P M20x1,5 D.6-12mm grey



Part number	19 00 000 5182
Specification	Han CGM-P M20x1,5 D.6-12mm grey
HARTING eCatalogue	https://b2b.harting.com/19000005182

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-P
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	4.5 Nm
Wrench size	A/F 24
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	6 ... 12 mm
Width across corners	26.4 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide
Colour (accessories)	RAL 7035 (light grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780



Pushing Performance

Specifications and approvals

CSA-C22.2 No. 18.3 QCRV7.E479780

Commercial data

Packaging size	10
Net weight	11.75 g
Country of origin	Germany
Customs tariff number	84849000
