

Han CGM-P M32x1,5 D.13-20mm grey



Part number	19 00 000 5194
Specification	Han CGM-P M32x1,5 D.13-20mm grey
HARTING eCatalogue	https://b2b.harting.com/19000005194

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-P
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	6.5 Nm
Wrench size	A/F 42
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M32
Clamping range	13 ... 18 mm
Width across corners	46.8 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide
Colour (accessories)	RAL 7035 (light grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780



Pushing Performance

Specifications and approvals

CSA-C22.2 No. 18.3 QCRV7.E479780

Commercial data

Packaging size	10
Net weight	42.94 g
Country of origin	Germany
Customs tariff number	84849000
