

## Han CGM-P M40x1,5 D.22-32mm grey



Part number	19 00 000 5198
Specification	Han CGM-P M40x1,5 D.22-32mm grey
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005198">https://b2b.harting.com/19000005198</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-P
Type of accessory	Cable gland

### Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	10 Nm
Wrench size	A/F 53
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	22 ... 32 mm
Width across corners	58.8 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide
Colour (accessories)	RAL 7035 (light grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780



Pushing Performance

## Specifications and approvals

---

CSA-C22.2 No. 18.3 QCRV7.E479780

---

## Commercial data

Packaging size	1
Net weight	68 g
Country of origin	Germany
Customs tariff number	84849000

---