

Cable Sealing M25x1,5 metal 10.5 - 14mm



Part number	19 12 000 5057
Specification	Cable Sealing M25x1,5 metal 10.5 - 14mm
HARTING eCatalogue	https://b2b.harting.com/19120005057

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods

Technical characteristics

Limiting temperature	-40 ... +130 °C
Tightening torque	10 Nm
Wrench size	A/F 28
Degree of protection acc. to IEC 60529	IP65
Size	M25
Clamping range	10.5 ... 14 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	10
Net weight	25.5 g
Country of origin	Germany



Pushing Performance

Commercial data

Customs tariff number	84849000
-----------------------	----------
