

## Han-Eco cable gland M32



Part number	19 41 000 5131
Specification	Han-Eco cable gland M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19410005131">https://b2b.harting.com/19410005131</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

### Technical characteristics

Limiting temperature	-20 ... +100 °C
Tightening torque	15 Nm Fitting 4 Nm Cap nut
Wrench size	A/F 36
Size	M32
Clamping range	13 ... 21 mm

### Material properties

Material (cable glands)	Polyamide
Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Commercial data

Packaging size	2
Net weight	33.7 g
Country of origin	Germany
Customs tariff number	39174000