

Han-Eco cable gland M40



Part number	19 41 000 5141
Specification	Han-Eco cable gland M40
HARTING eCatalogue	https://b2b.harting.com/19410005141

Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-20 ... +100 °C
Tightening torque	20 Nm Fitting 20 Nm Cap nut
Wrench size	A/F 46
Size	M40
Clamping range	16 ... 28 mm

Material properties

Material (cable glands)	Polyamide
Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	2
Net weight	61.9 g
Country of origin	Germany
Customs tariff number	39174000