




Pushing Performance

Acces. Special Cable Clamp EMC M20



| | |
|--------------------|---|
| Part number | 19 62 000 5080 |
| Specification | Acces. Special Cable Clamp EMC M20 |
| HARTING eCatalogue | https://b2b.harting.com/19620005080 |

Identification

| | |
|------------------------------|-------------|
| Category | Accessories |
| Type of accessory | Cable gland |
| Description of the accessory | EMC version |

Technical characteristics

| | |
|--|----------------|
| Wrench size | A/F 22 |
| Degree of protection acc. to IEC 60529 | IP68 |
| Size | M20 |
| Clamping range | 6.5 ... 9.5 mm |
| Shielding diameter | 3.5 ... 8.5 mm |
| Width across corners | 24.4 mm |

Material properties

| | |
|-----------------------------|--|
| Material (cable glands) | Metal |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Commercial data

| | |
|-------------------|---------|
| Packaging size | 10 |
| Net weight | 34.37 g |
| Country of origin | Germany |



Pushing Performance

Commercial data

| | |
|-----------------------|----------|
| Customs tariff number | 84849000 |
|-----------------------|----------|
