




Pushing Performance

## Acces. Special Cable Clamp EMC M32



Part number	19 62 000 5094
Specification	Acces. Special Cable Clamp EMC M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19620005094">https://b2b.harting.com/19620005094</a>

### Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

### Technical characteristics

Wrench size	A/F 35
Degree of protection acc. to IEC 60529	IP68
Size	M32
Clamping range	11.5 ... 15.5 mm
Shielding diameter	8 ... 13.5 mm
Width across corners	38.5 mm

### Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Commercial data

Packaging size	10
Net weight	102.41 g
Country of origin	Germany



Pushing Performance

## Commercial data

Customs tariff number	84849000
-----------------------	----------

---