




Pushing Performance

Acces. Special Cable Clamp EMC M40



Part number	19 62 000 5098
Specification	Acces. Special Cable Clamp EMC M40
HARTING eCatalogue	https://b2b.harting.com/19620005098

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Wrench size	A/F 43
Degree of protection acc. to IEC 60529	IP68
Size	M40
Clamping range	20 ... 25 mm
Shielding diameter	15 ... 20 mm
Width across corners	47.3 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	1
Net weight	146.8 g
Country of origin	Germany



Pushing Performance

Commercial data

Customs tariff number	84849000
-----------------------	----------
