

Han-Modular coax F-contact 50Ohm (RG174)



Part number	09 14 000 6211
Specification	Han-Modular coax F-contact 50Ohm (RG174)
HARTING eCatalogue	https://b2b.harting.com/09140006211

Identification

Category	Contacts
Series	DIN 41626
Type of contact	Coaxial contact
Description of the contact	for cables RG 174 U, 188 AU, 316 U

Version

Termination method	Solder/crimp termination
Gender	Male

Technical characteristics

Operating current	≤ 1.5 A
Contact resistance	≤ 10 m Ω
Impedance	50 Ω

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

IEC 61984

Commercial data

Packaging size	10
Net weight	2.16 g
Country of origin	Germany
Customs tariff number	85366910