

Han-Snap Latching parts w. strain relief



Part number	09 33 000 9991
Specification	Han-Snap Latching parts w. strain relief
HARTING eCatalogue	https://b2b.harting.com/09330009991

Identification

Category	Accessories
Series	Han-Snap®
Type of accessory	Latching parts
Description of the accessory	With strain relief

Version

Pack contents	1 latching part with strain relief 1 latching part
---------------	---

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque	0.8 Nm
Degree of protection acc. to IEC 60529	IP20
Retention force	200 N Without guiding 300 N With guiding

Material properties

Material (accessories)	Polycarbonate
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal)
----------------	--------------------------------------



Pushing Performance

Specifications and approvals

IEC 60068-2-27 Shock

Commercial data

Packaging size	10
Net weight	22.75 g
Country of origin	Germany
Customs tariff number	85389099