

Han 24 HPR EasyCon Cover 3XM25



Part number	19 40 024 9901
Specification	Han 24 HPR EasyCon Cover 3XM25
HARTING eCatalogue	https://b2b.harting.com/19400249901

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR EasyCon
Type of hood/housing	Mounting cover
Description of hood/housing	for surface mounted housings for hoods

Version

Locking type	Screw locking
Size	24 HPR
Cable gland	3x M25

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque	6 Nm Mounting cover
	6 Nm Distance bolt
	6 Nm Fixing screws
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	258 g
Country of origin	Germany
Customs tariff number	85389099