

Han 48HPR cover angled housing 4XM40



Part number	19 40 048 9801
Specification	Han 48HPR cover angled housing 4XM40
HARTING eCatalogue	https://b2b.harting.com/19400489801

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Mounting cover
Description of hood/housing	Distance bolt M5 for male inserts

Version

Locking type	Screw locking
Size	48 B
Cable gland	4x M40
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	4 distance pieces 4x M6 screw 4 washers

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	511.33 g
Country of origin	Germany
Customs tariff number	85389099