

Han-Eco Mod.-PE module-m 16-6 AWG



Part number	19 41 001 2600
Specification	Han-Eco Mod.-PE module-m 16-6 AWG
HARTING eCatalogue	https://b2b.harting.com/19410012600

Identification

Category	Modules
Series	Han-Eco® Modular
Type of module	Contact module

Version

Termination method	Screw termination
Gender	Male
Number of contacts	1
Details	With 09 99 000 0830 HARTING Crimping tool also cable up to 25 mm ² with ferrule adaptable Not for Han-Modular® hinged frames!

Technical characteristics

Conductor cross-section	1.5 ... 16 mm ²
Mating cycles	≥500

Material properties

Colour (insert)	RAL 7032 (pebble grey)
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight 6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	2
Net weight	39.04 g
Country of origin	Germany
Customs tariff number	85366990