

Yellock PE extension crimp 10mm²



| | |
|--------------------|---|
| Part number | 11 00 000 9510 |
| Specification | Yellock PE extension crimp 10mm ² |
| HARTING eCatalogue | https://b2b.harting.com/11000009510 |

Identification

| | |
|-----------------|--------------|
| Category | Contacts |
| Series | Han-Yellock® |
| Type of contact | PE contact |

Version

| | |
|--------------------|-------------------|
| Termination method | Crimp termination |
| Gender | Male |

Technical characteristics

| | |
|-------------------------|--------------------|
| Conductor cross-section | 10 mm ² |
| Conductor cross-section | AWG 8 |
| Operating current | ≤20 A |
| Contact resistance | ≤2 mΩ |
| Stripping length | 7.5 mm |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Silver plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|----------------|------------|
| Specifications | EN 60664-1 |
|----------------|------------|



Pushing Performance

Specifications and approvals

| |
|-----------|
| IEC 61984 |
|-----------|

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 3.3 g |
| Country of origin | Germany |
| Customs tariff number | 85366990 |