

Pneumatic contact female 4,0 mm



Part number	09 14 000 6253
Specification	Pneumatic contact female 4,0 mm
HARTING eCatalogue	https://b2b.harting.com/09140006253

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 +80 °C
Operating pressure	≤8 bar
Tube inner diameter	4 mm

Material properties

Material (contacts)	Delrin acetal
Material (seal)	Buna-N
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Material properties

REACH SVHC substances Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	0.24 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140018396
eCl@ss	27440204 Contact for industrial connectors