

## Pneumatic contact fem. with valve 4,0 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6258
Specification	Pneumatic contact fem. with valve 4,0 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09140006258">https://b2b.harting.com/09140006258</a>

### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Polypropylen Straight

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-40 ... +80 °C
Operating pressure	≤8 bar
Tube inner diameter	4 mm

### Material properties

Material (contacts)	Delrin acetal
Material (seal)	Buna-N
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

