

## Han PushPull PFT plastic Bulkhead Cat.6



Part number	09 35 225 0331
Specification	Han PushPull PFT plastic Bulkhead Cat.6
HARTING eCatalogue	<a href="https://b2b.harting.com/09352250331">https://b2b.harting.com/09352250331</a>
Features	Intuitive locking mechanism

### Identification

Category	Connector
Series	Han® PushPull
Identification	RJ45
Element	Panel feed trough set

### Version

Locking type	PushPull
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Pack contents	incl. housing and HARTING RJ Industrial® 10G RJ45 bulkhead

### Technical characteristics

Electrical data acc. to IEC 61984	1.75 A 50 V
Rated current	1.75 A
Rated voltage	50 V
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Transmission characteristics	Cat. 6 Class E up to 250 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 10 Gbit/s

### Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black



Pushing Performance

## Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61076-3-117 IEC 60603-7 Mating face
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	27.5 g
Country of origin	Germany
Customs tariff number	85389099