

Han-Modular Compact housing



Part number	09 14 001 0301
Specification	Han-Modular Compact housing
HARTING eCatalogue	https://b2b.harting.com/09140010301

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Compact
Type of hood/housing	Bulkhead mounted housings

Version

Locking type	Single locking lever
Size	Modular Compact

Technical characteristics

Limiting temperature	-40 ... +125 °C
Stripping length	10 mm PE contact
Tightening torque	1 Nm PE screw
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 in locked position

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	10
----------------	----



Pushing Performance

Commercial data

Net weight	82.97 g
Country of origin	Germany
Customs tariff number	85389099