

Han 3A-agg-QB-K Kappe ohne Dichtung



Part number	09 20 003 0305
Specification	Han 3A-agg-QB-K Kappe ohne Dichtung
HARTING eCatalogue	https://b2b.harting.com/09200030305

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Straight With metal cover

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for male inserts

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	63.8 g
Country of origin	Germany
Customs tariff number	85389099