

Han A Base Panel 4 Pegs Thermoplastic Co



Part number	09 20 032 0302
Specification	Han A Base Panel 4 Pegs Thermoplastic Co
HARTING eCatalogue	https://b2b.harting.com/09200320302

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	With thermo-plastic cover
Type	Low construction

Version

Locking type	Double locking lever (on the hood)
Size	32 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	71.94 g
Country of origin	Germany
Customs tariff number	85389099
