

## Han 10B-agg-K (Ak in Al)



Part number	09 30 010 0317
Specification	Han 10B-agg-K (Ak in Al)
HARTING eCatalogue	<a href="https://b2b.harting.com/09300100317">https://b2b.harting.com/09300100317</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	With metal cover
Type	Low construction

### Version

Locking type	Double locking lever (on the hood)
Size	10 B
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

---

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	127.12 g
Country of origin	Germany
Customs tariff number	85389099

---