

Han 16B-HBM single lever metal cover



Part number	09 30 016 0318
Specification	Han 16B-HBM single lever metal cover
HARTING eCatalogue	https://b2b.harting.com/09300160318
Identification	
Category	Hoods/Housings
Series of hoods/housingsHan [®] B	
Type of hood/housing	Bulkhead mounted housings
Description of hood/ housing	With metal cover
Туре	Low construction

Version

Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Size	16 B
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant

Page 1 / 2 | Creation date 2018-09-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 NO. 182.3 ECB18.E233076

Commercial data

Packaging size	1
Net weight	181.8 g
Country of origin	Germany
Customs tariff number	85389099