

# Han 16B-Base Panel 2 Levers IP67



Part number	09 30 016 1301
Specification	Han 16B-Base Panel 2 Levers IP67
HARTING eCatalogue	https://b2b.harting.com/09300161301
Identification	
Category	Hoods/Housings
Series of hoods/housings Han <sup>®</sup> B	
Series of hoods/housing	s Han <sup>®</sup> B
Series of hoods/housing	<sup>S</sup> Han <sup>®</sup> B Bulkhead mounted housings

### Version

Locking type	Double locking lever
Han-Easy Lock <sup>®</sup>	Yes
Size	16 B
Field of application	Standard hoods/housings for industrial connectors

## **Technical characteristics**

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

# Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant

Page 1 / 2 | Creation date 2018-09-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	135.6 g
Country of origin	China
Customs tariff number	8538900000