

Han M Base Panel 1 Lever Cover



Part number	09 37 003 0305
Specification	Han M Base Panel 1 Lever Cover
HARTING eCatalogue	https://b2b.harting.com/09370030305

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Straight With metal cover With seal

Version

Locking type	Single locking lever
Size	3 A
Field of application	Hoods/housings for rough environments
Details	for male inserts

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
----------------	----

Net weight	64.88 g
------------	---------

Country of origin	Germany
-------------------	---------

Customs tariff number	85389099
-----------------------	----------