

## Han 3HPR-HBM-TL-black chrome



Part number	09 40 003 0301
Specification	Han 3HPR-HBM-TL-black chrome
HARTING eCatalogue	<a href="https://b2b.harting.com/09400030301">https://b2b.harting.com/09400030301</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Straight

### Version

Locking type	Toggle locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	With seal screw

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances No

---

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

---

## Commercial data

Packaging size	10
Net weight	53.4 g
Country of origin	Germany
Customs tariff number	85389099

---