

# Han 3HPR angled housing



Part number	09 40 003 0950
Specification	Han 3HPR angled housing
HARTING eCatalogue	https://b2b.harting.com/09400030950

## Identification

Category	Hoods/Housings
Series of hoods/housingsHan® HPR	
Type of hood/housing	Bulkhead mounted housings
Description of hood/ housing	Angled
	Open bottom
	Feed through hole for fixing screws

#### Version

Locking type	Screw locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	With seal screw

### Technical characteristics

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	2 Nm
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	е



# Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

# Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

Packaging size	1
Net weight	142.8 g
Country of origin	Germany
Customs tariff number	85389099