

# Han 10HPR-HBM-Toggle locking



Part number	09 40 010 0301
Specification	Han 10HPR-HBM-Toggle locking
HARTING eCatalogue	https://b2b.harting.com/09400100301

## Identification

Category	Hoods/Housings
Series of hoods/housings	<sup>8</sup> Han <sup>®</sup> HPR
Type of hood/housing	Bulkhead mounted housings

## Version

Locking type	Toggle locking
Size	10 B
Field of application	Hoods/housings for harsh outdoor environments

## Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

# Material properties

Aluminium die-cast Corrosion resistant
Powder-coated
RAL 9005 (jet black)
NBR
compliant
compliant
е
No
No
No



# Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

# Commercial data

Packaging size	1
Net weight	155.7 g
Country of origin	Germany
Customs tariff number	85389099