

## Han 48 HPR Base Panel



Part number	09 40 048 0331
Specification	Han 48 HPR Base Panel
HARTING eCatalogue	<a href="https://b2b.harting.com/09400480331">https://b2b.harting.com/09400480331</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HPR
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	for 4 standard inserts - size 16 B

### Version

Locking type	Screw locking
Size	48 B
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
----------------	---

Net weight	710.68 g
------------	----------

Country of origin	Germany
-------------------	---------

Customs tariff number	85389099
-----------------------	----------