

## Han 3HPR angled hous. long, RoHS conf.



Part number	09 40 703 0951
Specification	Han 3HPR angled hous. long, RoHS conf.
HARTING eCatalogue	<a href="https://b2b.harting.com/09407030951">https://b2b.harting.com/09407030951</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Angled
	Open bottom
	Long version
	Feed through hole for fixing screws

### Version

Locking type	Screw locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	With seal screw

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	2 Nm
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
	FPM
RoHS	compliant



Pushing Performance

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	204.4 g
Country of origin	Germany
Customs tariff number	85389099