

Han 3HPR angled hous. long, RoHS conf.



| Part number | 09 40 703 0953 |
|---------------------------------|---|
| Specification | Han 3HPR angled hous. long, RoHS conf. |
| HARTING eCatalogue | https://b2b.harting.com/09407030953 |
| Identification | |
| Category | Hoods/Housings |
| Series of hoods/housing | ISHan [®] HPR |
| Type of hood/housing | Bulkhead mounted housings |
| | Angled |
| Description of hood/ housing | Open bottom |
| | |
| nousing | Long version |
| nousing | Long version Tapped blind hole for fixing screws |

Version

| Locking type | Screw locking |
|----------------------|---|
| Size | 3 A |
| Field of application | Hoods/housings for harsh outdoor environments |
| Pack contents | With seal screw |

Technical characteristics

| Limiting temperature | -40 +125 °C |
|--|--|
| Tightening torque (screw locking) | 2 Nm |
| Degree of protection acc. to IEC 60529 | IP65 IP68 IP69 / IPX9K acc. to ISO 20653 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| Material (hood/housing) | Zinc die-cast |
|-------------------------|----------------------|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| | FPM |
| RoHS | compliant |

Page 1 / 2 | Creation date 2018-08-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

| ELV status | compliant |
|-----------------------------|-----------|
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| Approvals | DNV GL |
|-----------|-----------------------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
| | CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| Packaging size | 1 |
|-----------------------|----------|
| Net weight | 216 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |