

# Han EMV 40 Base Panel



| Part number        | 09 62 040 0301                      |
|--------------------|-------------------------------------|
| Specification      | Han EMV 40 Base Panel               |
| HARTING eCatalogue | https://b2b.harting.com/09620400301 |

#### Identification

| Category                         | Hoods/Housings            |  |
|----------------------------------|---------------------------|--|
| Series of hoods/housingsHan® EMC |                           |  |
| Type of hood/housing             | Bulkhead mounted housings |  |

### Version

| Locking type         | Screw locking                              |
|----------------------|--|
| Size                 | 16 B                                       |
| Field of application | Hoods/Housings for higher EMC requirements |

#### Technical characteristics

| Limiting temperature                   | -40 +125 °C |
|--|-------------|
| Degree of protection acc. to IEC 60529 | IP65        |
| Type rating acc. to UL 50 / UL 50E     | 4           |
|  | 12          |

## Material properties

| Material (hood/housing)     | Aluminium die-cast |
|-----------------------------|--------------------|
| Surface (hood/housing)      | Uncoated           |
| Colour (hood/housing)       | Unpainted          |
| Material (seal)             | NBR                |
| RoHS                        | compliant          |
| ELV status                  | compliant          |
| China RoHS                  | е                  |
| REACH Annex XVII substances | No                 |
| REACH ANNEX XIV substances  | No                 |
| REACH SVHC substances       | No                 |

# Specifications and approvals

|--|



# Specifications and approvals

UL / CSA UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

| Packaging size        | 1        |
|-----------------------|----------|
| Net weight            | 123.5 g  |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |