

## Han-Yellock 60 bulkhead hsg-Molly Bolts



|                    |   |
|--------------------|---|
| Part number        | 11 12 600 0302  |
| Specification      | Han-Yellock 60 bulkhead hsg-Molly Bolts   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/11126000302">https://b2b.harting.com/11126000302</a> |

### Identification

|                          |                           |
|--------------------------|---------------------------|
| Category                 | Hoods/Housings            |
| Series of hoods/housings | Han-Yellock®              |
| Type of hood/housing     | Bulkhead mounted housings |

### Version

|                      |  |
|----------------------|--|
| Size                 | Han-Yellock® 60                            |
| Field of application | Hoods/housings for industrial applications |
| Pack contents        | incl. 4 panel fastener                     |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Un-/locking temperature                | -10 ... +85 °C  |
| Degree of protection acc. to IEC 60529 | IP65<br>IP67    |

### Material properties

|   |               |
|---|---------------|
| Material (hood/housing)                   | Zinc die-cast |
| Surface (hood/housing)                    | Passivated    |
| Colour (hood/housing)                     | Metallic      |
| Material (seal)                           | NBR           |
| Material flammability class acc. to UL 94 | V-0           |
| RoHS                                      | compliant     |
| ELV status                                | compliant     |
| China RoHS                                | e             |
| REACH Annex XVII substances               | No            |
| REACH ANNEX XIV substances                | No            |
| REACH SVHC substances                     | No            |



Pushing Performance

## Specifications and approvals

|                |                         |
|----------------|-------------------------|
| Specifications | EN 60664-1<br>IEC 61984 |
| Approvals      | DNV GL                  |

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 1        |
| Net weight            | 152.8 g  |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |