

## Han-Yellock 30 bulkhead housing



Part number	11 13 300 0301
Specification	Han-Yellock 30 bulkhead housing
HARTING eCatalogue	<a href="https://b2b.harting.com/11133000301">https://b2b.harting.com/11133000301</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Bulkhead mounted housings

### Version

Size	Han-Yellock® 30
Field of application	Hoods/housings for outdoor applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

## Specifications and approvals

Approvals DNV GL

---

## Commercial data

Packaging size	1
Net weight	117.8 g
Country of origin	Germany
Customs tariff number	85389099

---