

Han-Yellock 30M-HBM (w. Molly Bolts)



Part number	11 13 300 0302
Specification	Han-Yellock 30M-HBM (w. Molly Bolts)
HARTING eCatalogue	https://b2b.harting.com/11133000302

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Bulkhead mounted housings

Version

Size	Han-Yellock® 30
Field of application	Hoods/housings for outdoor applications
Pack contents	incl. 4 panel fastener

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

	IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	127 g
Country of origin	Germany
Customs tariff number	85389099