

## Han-Yellock 10 bulkhead mount housing



Part number	11 20 003 0300
Specification	Han-Yellock 10 bulkhead mount housing
HARTING eCatalogue	<a href="https://b2b.harting.com/11200030300">https://b2b.harting.com/11200030300</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Straight

### Version

Locking type	Push button
Size	Han-Yellock® 10
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Zinc passivation
Colour (hood/housing)	Metallic
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	61 g
Country of origin	Germany
Customs tariff number	85389099