

Han-Yellock 10 HABM



| | |
|--------------------|---|
| Part number | 11 20 003 0800 |
| Specification | Han-Yellock 10 HABM |
| HARTING eCatalogue | https://b2b.harting.com/11200030800 |

Identification

| | |
|-----------------------------|---------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Yellock® |
| Type of hood/housing | Bulkhead mounted housings |
| Description of hood/housing | Angled |

Version

| | |
|----------------------|--|
| Locking type | Push button |
| Size | Han-Yellock® 10 |
| Field of application | Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Un-/locking temperature | -10 ... +85 °C |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |

Material properties

| | |
|---|------------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Zinc passivation |
| Colour (hood/housing) | Metallic |
| Material (seal) | NBR |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |



Pushing Performance

Material properties

| | |
|-----------------------|----|
| REACH SVHC substances | No |
|-----------------------|----|

Specifications and approvals

| | |
|----------------|-------------------------|
| Specifications | EN 60664-1 IEC 61984 |
| Approvals | DNV GL |

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 155.7 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |