

# Han 3A base screw M20



Part number	19 20 003 1150
Specification	Han 3A base screw M20
HARTING eCatalogue	https://b2b.harting.com/19200031150

### Identification

Category	Hoods/Housings	
Series of hoods/housings Han A <sup>®</sup>		
Type of bood/housing	Screw mounted housings	

#### Version

Locking type	Single locking lever
Size	3 A
Cable entry	1x M20
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918

# Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	<ul><li>6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight</li><li>6c: Copper alloy containing up to 4 % lead by weight</li></ul>
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



## Material properties

REACH SVHC substances Lead

## Specifications and approvals

Approvals DNV GL

#### Commercial data

Packaging size	10
Net weight	57.71 g
Country of origin	Germany
Customs tariff number	85389099