

Han A Hood Coupler Thermoplastic 1 Lever



Part number	19 20 003 0727	
Specification	Han A Hood Coupler Thermoplastic 1 Lever	
HARTING eCatalogue	https://b2b.harting.com/19200030727	
Identification		
Category	Hoods/Housings	
Series of hoods/housingsHan A [®]		
Type of hood/housing	Cable to cable housing	

Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable entry	1x M20
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No

Page 1 / 2 | Creation date 2018-09-04 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties	
REACH SVHC substances	No
Specifications and approvals	
Approvals	DNV GL
Commercial data	
Packaging size	10
Net weight	16.5 g
Country of origin	Romania
Customs tariff number	85389099