

## Han B Hood Coupler LC M32



|                    |   |
|--------------------|---|
| Part number        | 19 30 016 1732  |
| Specification      | Han B Hood Coupler LC M32   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19300161732">https://b2b.harting.com/19300161732</a> |

### Identification

|                          |                        |
|--------------------------|------------------------|
| Category                 | Hoods/Housings         |
| Series of hoods/housings | Han <sup>®</sup> B     |
| Type of hood/housing     | Cable to cable housing |
| Type                     | Low construction       |

### Version

|                            |   |
|----------------------------|---|
| Locking type               | Double locking lever                              |
| Han-Easy Lock <sup>®</sup> | Yes   |
| Size                       | 16 B  |
| Version                    | Top entry   |
| Cable entry                | 1x M32  |
| Field of application       | Standard hoods/housings for industrial connectors |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12   |

### Material properties

|  |                                  |
|--|----------------------------------|
| Material (hood/housing)                                    | Aluminium die-cast               |
| Surface (hood/housing)                                     | Powder-coated                    |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)             |
| Material (seal)  | NBR                              |
| Material (locking)   | Polycarbonate<br>Stainless steel |
| Colour (locking)   | RAL 7037 (dust grey)             |
| Material flammability class acc. to UL 94 (locking levers) | V-0                              |



Pushing Performance

## Material properties

|                             |           |
|-----------------------------|-----------|
| RoHS                        | compliant |
| ELV status                  | compliant |
| China RoHS                  | e         |
| REACH Annex XVII substances | No        |
| REACH ANNEX XIV substances  | No        |
| REACH SVHC substances       | No        |

## Specifications and approvals

|           |  |
|-----------|--|
| Approvals | DNV GL   |
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 1        |
| Net weight            | 183.25 g |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |