

## Han 6HvE-kg-QB-M25



Part number	19 34 006 0731
Specification	Han 6HvE-kg-QB-M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19340060731">https://b2b.harting.com/19340060731</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han Hv E®
Type of hood/housing	Cable to cable housing
Type	Low construction

### Version

Locking type	Double locking lever
Han-Easy Lock®	Yes
Size	16 B
Version	Top entry
Cable entry	1x M25
Field of application	Special hoods/housings for Han Hv E® screw terminal

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0



Pushing Performance

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	197.1 g
Country of origin	Germany
Customs tariff number	85389099