

## Han-Eco Mod.16 Outd.-HCC-M40-glanded



Part number	19 41 316 0723
Specification	Han-Eco Mod.16 Outd.-HCC-M40-glanded
HARTING eCatalogue	<a href="https://b2b.harting.com/19413160723">https://b2b.harting.com/19413160723</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® Modular
Type of hood/housing	Cable to cable housing
Description of hood/housing	With integrated cable gland

### Version

Locking type	Double locking lever
Size	16 B
Version	Top entry
Cable entry	1x M40

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Clamping range	16 ... 28 mm

### Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant



Pushing Performance

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	249 g
Country of origin	Germany
Customs tariff number	85389099