

Han Snap Plastic Housing Size 6



Part number	09 33 006 0401
Specification	Han Snap Plastic Housing Size 6
HARTING eCatalogue	https://b2b.harting.com/09330060401

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Snap®
Type of hood/housing	Shell housing

Version

Locking type	Snap-in latches
Size	6 B
Version	Top/side entry
Pack contents	2 half shells with blind plugs

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque	0.8 Nm
Retention force	≥300 N in locked position

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal)
----------------	--------------------------------------



Pushing Performance

Specifications and approvals

IEC 60068-2-27 Shock

Commercial data

Packaging size	1
Net weight	0.58 g
Country of origin	Germany
Customs tariff number	85389099