

## Han M Base Surface 1 Lever 1 Entry PG 11



Part number	09 37 003 1250
Specification	Han M Base Surface 1 Lever 1 Entry PG 11
HARTING eCatalogue	<a href="https://b2b.harting.com/09370031250">https://b2b.harting.com/09370031250</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M
Type of hood/housing	Surface mounted housing

### Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable gland	1x Pg 11
Field of application	Hoods/housings for rough environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	86.9 g
Country of origin	Germany
Customs tariff number	85389099