

Han Yellock 30HSM 1xM20 with bulkhead h.



| | |
|--------------------|---|
| Part number | 11 12 300 1210 |
| Specification | Han Yellock 30HSM 1xM20 with bulkhead h. |
| HARTING eCatalogue | https://b2b.harting.com/11123001210 |

Identification

| | |
|-----------------------------|---------------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Yellock® |
| Type of hood/housing | Surface mounted housing |
| Description of hood/housing | incl. bulkhead mounted housings |

Version

| | |
|----------------------|--|
| Locking type | Screw locking |
| Size | Han-Yellock® 30 |
| Version | Side entry |
| Cable entry | 1x M20 |
| Field of application | Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Un-/locking temperature | -10 ... +85 °C |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |

Material properties

| | |
|---|-----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7021 (black grey) |
| Material (seal) | NBR |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Specifications EN 60664-1
IEC 61984

Approvals DNV GL

Commercial data

Packaging size 1

Net weight 535 g

Country of origin China

Customs tariff number 85389099